



## Product Data Sheet

### **AmberLite™ FPA40 Cl**

Food Grade Strong Base Anion Exchanger

#### **Introduction**

AmberLite™ FPA40 Cl can be used as an alternative to AmberLite™ FPA98 Cl or AmberLite™ FPA90 Cl to decolorize sugar solutions < 200 ICUMSA.

Whilst a gellular resin, the high moisture content exhibits some of the characteristics of a macro-reticular resin which make AmberLite™ FPA40 Cl ideally suited to the reversible uptake of organic color bodies commonly found in sucrose syrups.

AmberLite™ FPA40 Cl is a very unique product in that it is a gellular resin (high capacity) with macroreticular characteristics (physical stability). It is an excellent resin of choice for Decolorization of organic color bodies in many bioprocessing applications, including natural product extraction and recovery / decolorization of antibiotics from fermentation broth.

It is extensively used in aminoglycoside purification processes in combination with AmberLite™ FPC3500, and/or AmberLite™ CG50 type 1.

Thanks to AMBERITE FPA40 Cl, higher level of purity of aminoglycoside antibiotics can be achieved in a deco-lorization step either pre- or post- purification.

#### **Properties**

AmberLite™ FPA40 Cl is a type 1 strong base anion exchange resin supplied in the Chloride form. Due to the relatively high moisture content, AmberLite™ FPA40 Cl exhibits some of the characteristics of macroreticular resin with good resistance to fouling and osmotic stress. The structure is particularly well suited to reversibly removing relatively large organic molecules from a variety of process streams.

Matrix	Crosslinked polystyrene
Functional groups	Quaternary ammonium
Physical form	Clear yellow beads
Ionic form as shipped	Chloride
Total exchange capacity	≥ 1.0 eq/L (Cl <sup>-</sup> form)
Moisture holding capacity	57 to 68 % (Cl <sup>-</sup> form)
Shipping weight	700 g/L
Harmonic mean size	0.50 to 0.75 mm
Fines content	< 0.425 mm : 2.0 % max

#### **Suggested Operating Conditions**

Operating temperature limit	60°C (OH <sup>-</sup> form) / 90°C (Cl <sup>-</sup> form)
Minimum bed depth	700 mm
Service flow rate	2 to 8 BV*/h
Regenerants	NaCl (4-10 %)
Regenerant level	50 to 150 g/LR
Regenerant flow rate	2 to 8 BV/h
Minimum contact time	30 minutes
Slow rinse	2 BV at regeneration flow rate
Fast rinse	4 to 8 BV at service flow rate

## Hydraulic Characteristics

Figure 1 shows the bed expansion of AmberLite™ FPA40 Cl, as a function of backwash flow rate and water temperature.

### Conversion Factors:

- 1 m/h equals 0.41 USgpm/ft<sup>2</sup>




Figure 1:

## Product Stewardship

DuPont has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with DuPont products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

## Customer Notice

DuPont strongly encourages its customers to review both their manufacturing processes and their applications of DuPont products from the standpoint of human health and environmental quality to ensure that DuPont products are not used in ways for which they are not intended or tested. DuPont personnel are available to answer your questions and to provide reasonable technical support. DuPont product literature, including safety data sheets, should be consulted prior to use of DuPont products. Current safety data sheets are available from DuPont.

Please be aware of the following:

- **WARNING:** Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.

**Have a question? Contact us at:**

[www.dupont.com/water/contact-us](http://www.dupont.com/water/contact-us)

All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

© 2022 DuPont. DuPont™, the DuPont Oval Logo, and all trademarks and service marks denoted with ™, SM or ® are owned by affiliates of DuPont de Nemours Inc., unless otherwise noted.

